

| | |
|-------------------------|------------------------------|
| Product Class | CeraLink B58035U* |
| Date | 04.10.2019 |
| IMDS ID if available | |
| Version | 5.04 |

| Product Part (IMDS: semi component) | Material Class (IMDS: Material) | Material (Classification) VDA 231 | Substance | TMPS** [wt%] | CAS if applicable | typical mass of material [wt-%] | Traces see 1) |
|---|------------------------------------|---|------------------|-----------------|------------------------|---------------------------------------|------------------|
| Active Part | Ceramic | 3B | PLZT others*) | 98 2 | 106390-68-5 | 85 | |
| Inner Electrode | Heavy Metal | 1C12 | Cu | 100 | 7440-50-8 | 8 | |
| Termination | Noble Metal | 1D7 | Ag | 100 | 7440-22-4 | 0.4 | |
| | Heavy Metal | 1C14 | Ni | 100 | 7440-02-0 | | < 0,001 |
| | Heavy Metal | 1C2 | Cr | 100 | 7440-47-3 | | < 0,001 |
| Contact | Steel and Iron | 1A | Fe Ni | 64 36 | 7439-89-6 7440-02-0 | 3.4 | |
| | Heavy Metal | 1C12 | Cu | 100 | 7440-50-8 | 2.6 | |
| | Noble Metal | 1D7 | Ag | 100 | 7440-22-4 | 0.2 | |
| | Glue | Duromer | 2D | Epoxy | 100 | | 0.4 |
| Sum of total | | | | | | 100 | |

| sizes [mm] | weight range [g] | material numbers | part numbers | sizes [mm] | weight range [g] | material numbers | part numbers |
|-----------------|--------------------|------------------|--------------|----------------|--------------------|------------------|--------------|
| 7.3 x 9.1 x 7.1 | 2.3 | B58035U5205M 62 | FA2 | 7.3 x 9.1 x 30 | 11.6 | B58035U5106M 1 | FA10 |
| 7.3 x 9.1 x 7.1 | 2.3 | B58035U7105M 62 | FA2 | 7.3 x 9.1 x 30 | 11.6 | B58035U7505M 1 | FA10 |
| 7.3 x 9.1 x 7.1 | 2.3 | B58035U9504M 62 | FA2 | 7.3 x 9.1 x 30 | 11.6 | B58035U9255M 1 | FA10 |
| 7.3 x 9.1 x 9.0 | 3.5 | B58035U5305M 62 | FA3 | | | | |
| 7.3 x 9.1 x 9.0 | 3.5 | B58035U7155M 62 | FA3 | | | | |
| 7.3 x 9.1 x 9.0 | 3.5 | B58035U9754M 62 | FA3 | | | | |

Not part of a Product Class

| | | |
|-----------------|--|---|
| Contact | Ronner Christoph | Important remarks: 1) The declaration limit is 0.1% as defined by IEC 62474 (IEC PAS 61906). Traces are product parts, substances etc. that are below a percentage of 0.1 % by weight, if not otherwise regulated. 2) This Material Data Sheet contains typical values of the respective products set forth herein. We expressly point out that all values and statements contained herein are based on our best present knowledge and cannot be regarded as binding statements or binding product specifications, unless otherwise explicitly agreed in writing. TDK ELECTRONICS AG AND ITS AFFILIATES HEREBY EXPRESSLY DISCLAIM ANY REPRESENTATION OR WARRANTY, WHETHER EXPRESS, IMPLIED OR STATUTORY, WITH REGARD TO THE STATEMENTS AND VALUES CONTAINED HEREIN, INCLUDING BUT NOT LIMITED TO ANY REPRESENTATION OR WARRANTY OF MERCHANTABILITY OR SUITABILITY FOR ANY PURPOSE. |
| Division | PPD Q QM | |
| Address | 8530 Deutschlandsberg, AUSTRIA | |
| | Tel: +43 3462 800 2139 mailto: functional.ppd-egpm.db@tdk-electronics.tdk.com | |

The products set forth herein are "RoHS-compatible". RoHS-compatible means that products are compatible with the requirements according to Art. 4 (substance restrictions) of Directive 2011/65/EU of the European Parliament and of the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

RoHS - Exemptions for the Product Class / Product according to Annex III: (valid not valid)

no exemptions;

- Exemption 6 (a): Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0,35 % lead by weight;
- Exemption 6 (b): Lead as an alloying element in aluminium containing up to 0,4 % lead by weight;
- Exemption 6 (c): Copper alloy containing up to 4 % lead by weight;
- Exemption 7 (a): Lead in high melting temperature type solder (i.e. lead-based alloys containing 85 % by weight or more lead);
- Exemption 7 (c)-I: Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound;
- Exemption 7 (c)-II: Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher;
- Exemption 7 (c)-III: Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC;
- Exemption 15: Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit Flip Chip packages;
- Other Exemption than above